

THE IQ-3300 REFLECTS YOUR PERFORMANCE

- Back reflection from -15 to -55 dB
- Fully programmable
- Reflection monitoring port included




Why Do I Need a Variable Back Reflector?

It is well known that optical reflections cause problems in many of today's high performance fiberoptic networks. When designing or evaluating these systems (or components), it is important to determine their sensitivity to reflection. By introducing a precise calibrated reflection, system performance (bit error rate, noise levels, or distortion) can be monitored and evaluated. Appropriate measures (isolators, directional couplers, APC connectors, etc.) can then be introduced to safeguard the system. Alternatively, you may find that your system is relatively immune to reflections and that costly, low reflection components are unnecessary.

The IQ Solution

As part of the IQ family, the IQ-3300 back reflector module integrates advanced testing applications with a simple, easy-to-use graphical user interface. The Windows™ application software ensures a rapid learning curve and provides impressive flexibility. Custom applications for automatic testing or monitoring can easily be created.



The IQ-3300 Variable Back Reflector

The IQ-3300 Variable Back Reflector consists of a variable attenuator and a precision mirror coupled to an input port, an output port, and a monitor port. The internal variable attenuator varies the intensity of the reflected light coupled back into the system. The monitor port provides access for direct monitoring of the reflected power.

The IQ-3300 Variable Back Reflector is Ideal for these Typical Applications:



Source power stability measurements: requires an IQ-3300 Variable Back Reflector and an IQ-1100 Power Meter

Other Applications:

- Bit error rate vs. return loss
- characterization
- Source power stability measurements
- Source spectral stability measurements
- System noise performance tests
- Distortion tests
- · Return loss meter certification

Testing Tip


When performing source stability measurements, use the IQ-3300 program feature to create an automatic reflection scan.

Three Different Display Modes

Display reflection settings as absolute, relative, or X+B (offset) values.

Customize

Depending on your specific requirements, wavelength and step size parameters are easily customized. The spectral resolution is 0.1 nm and the minimum step size is 0.01 dB.



Powerful Program Mode

Use the program mode to quickly create automatic reflection scans. Up to 100 program steps with a maximum dwell time of 99 hours for each step.

Fine Tune Reflection Setting

Press the Up or Down buttons to change the reflection one step. Step sizes between 0.01 dB and 40.00 dB may be selected.

Edit the displayed value to precisely set a specific reflection.

High Isolation Shutter

The shutter instantly isolates the mirror from the optical circuit ensuring lower than -55 dB reflectance.

Impressive Performance

- Calibrated reflection to -55 dB
- ±0.5 dB accuracy
- ±0.2 dB linearity
- ±0.06 dB repeatability
- 0.01 dB resolution
- 1270 to 1350 and 1510 to 1590 nm spectrum
- 0.1 nm spectral resolution
- Low insertion loss
- Low polarization dependent loss (PDL)

User-Friendly Graphical Interface

- Windows™ compatible
- Easy control with software buttons, front panel keys, or keyboard
- Multiple-user configuration storage
- Simultaneous multiple applications for true multitasking
- · On-line help

OPTICAL SPECIFICATIONS

Fiber type (µm)	9/125	
Wavelength range ¹ (nm)	1270 to 1350	1510 to 1590
Reflection range (dB)	-15 to -55	
Insertion loss (in-out) ² (dB)	5	
Resolution (dB)	0.01	
Accuracy³ (dB)	±0.5	
Linearity ⁴ (dB)	±0.2	
Repeatability (dB)	±0.06	
Maximum input power⁵ (dBm)	22	
PDL (dB) max.	0.4	
Reflection with shutter (dB)	<-55	

MECHANICAL SPECIFICATIONS

Temperature	operating	0 to 50°C	32 to 122°F
	storage	-40 to 70°C	-40 to 158°F
Relative humidity ⁶		0 to 95% non-condensing	
Dimensions (H x W	/ x D)	12 x 3.8 x 26.2 cm	
		$4^{3}/_{4} \times 1^{1}/_{2} \times 10^{5}/_{16} \text{ in}$	
Weight		0.80 kg	1.76 lb

NOTES

- 1. Calibrated at 1310 nm and 1550 nm, wavelength corrections are performed by software.
- 2. Insertion loss includes unit connectors.
- 3. Using APC connectors.
- 4. Obtained at 23 ±2°C, using a light source of 0.002 dB stability during a 15 minute period (source accuracy of ±0.5 nm) with non-polarized light and at calibrated wavelength.
- Input power above this limit may damage the unit. The linearity specification may be higher than specified.
- 6. Measured in 0° to 40°C (32 to 104°F) temperature range.

Specifications subject to change without notice.

ORDERING INFORMATION

IQ-3300-<u>XX</u>

Connector code

58 = FC/APC

86 = DIN 47256 (LSA)/APC

88 = SC/APC

EI = EXFO UPC Interface

EA = EXFO APC Interface

The fixed base-plate (EA) must be ordered with a removable universal connector adapter EUI-XX. Please specify one EUI from the following list:

EUI-28= DIN 47256

EUI-89= FC

EUI-91= SC

EUI-95= E-2000

STANDARD ACCESSORIES

- IQ-3300 module c/w APC connectors
- Test jumper
- Calibration mandrel
- Instruction manual
- Certificate of Compliance

OPTIONAL ACCESSORIES

- LabVIEW drivers available
- OCX controls available in IQ-SDK

EXFO is certified **ISO 9001** and attests to the quality of its products. These products are accompanied by a 24-month warranty and an excellent aftersales support service.

Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

These devices comply with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) these devices may not cause harmful interference, and (2) these devices must accept any interference received, including interference that may cause undesired operation.

EXFO has made every effort to ensure that the information contained in this brochure is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics, and products at any time without obligation.





1-800-663-3936 info@exfo.com www.exfo.com



CORPORATE HEADQUARTERS: 465 Godin Avenue, Vanier, Quebec, G1M 3G7, Canada Tel.: (418) 683-0211 Fax: (418) 683-2170 EXFO AMERICA: 903 North Bowser, Suite 360, Richardson, TX, 75081, USA Tel.: 1-800-663-EXFO Fax: (972) 907-2297 EXFO EUROPE: Centre d'Affaires-Les Metz, 100, rue Albert Calmette, 78353 Jouy-en-Josas, France Tel.: +33 1 34 63 00 20 Fax: +33 1 34 65 90 93