## **ERBIUM-DOPED FIBER AMPLIFIER**

IQS-6100

R&D AND MANUFACTURING





## Investigate, Calibrate and Verify


The IQS-6100 Erbium-Doped Fiber Amplifier (EDFA) is part of the IQS-500 Intelligent Test System, EXFO's unmatched modular-concept test unit. The addition of an optical amplifier offers considerable flexibility to a WDM active component test setup. Use the EDFA to investigate non-linear effects such as four-wave mixing, or to calibrate and verify power meters, photodetectors and attenuators at high power levels.




#### **KEY FEATURES**

- User-friendly operation
- Easy one-slot IQS-500 module insertion
- Compatible with EXFO tunable laser sources

# Boost the tunable laser source and obtain high power over the entire C-band.





## Stability

The IQS-6100 attains a maximum drift of  $\pm$  0.01 dB, preserving input signal stability. Combine this EDFA with the EXFO IQS-2600B Tunable Light Source or the IQS-2400 WDM Laser Source to evaluate non-linear properties of optical materials in the 1550 nm band.




IQS-2600B Tunable Light Source, IQS-2400 WDM Laser Source

#### Powerful Versatility

For use with single or multiple wavelength signals, this optical amplifier increases output power from 0 dBm up to 15 dBm. Ideal for integration in WDM active component test setups, it enables the adjustment of WDM signals to the total input power level required for system or booster-amplifier modules. Achieve adequate power levels conveniently with this C-band amplifier.

#### **High power**

Add an EDFA booster to increase the flexibility of your WDM active component testing platform. Easily adjust multiple signals to the total input power level required for higher power subsystem characterization.



### An active component testing solution

The IQS-6100 EDFA booster is the perfect instrument for attaining higher power levels and minimizing insertion loss in linearity evaluations of photosensitive devices. Here's how it works:

#### STEP 1

Use a stable, optically isolated DFB laser source to reduce sensitivity to reflection.

#### STEP 2


Split the power into two branches. Use a coupler of different lengths to avoid Mach-Zehnder interference fluctuations, then recombine the branches.

#### STEP 3

Use inserted variable optical attenuators (VOA) to obtain identical power from both branches at the testing point.

#### STEP 4

Use the superposition method to characterize DUT linearity.



Typical setup for measuring the optical linearity of power meters with the superposition method. The IQS-6100 compensates for the insertion loss introduced by the coupler.



Wavelength range (nm)		1530 to 1560			
Saturated output power (dBm) at 3 dBm input power					
	typical	>14			
	minimum	13			
	maximum	15			
Noise figure (dB)	typical	8			
Output power stability <sup>1</sup> (dB)		$\pm 0.01 \ (\Delta = 0.02)$			
Polarization dependent gain (dB)		< 0.2			
Optical return loss (dB)	typical	35			
Small signal gain (dB) <sup>2</sup>	minimum	29			

#### Notes

- 1. Over 15 minutes after a 1-hour warm-up with a stable input source.
- 2. At input power of -20 dBm.

#### **GENERAL SPECIFICATIONS**

Operating Temperature		0 °C to 40 °C	(32 °F to 104 °F)	
Storage Temperature		-40 °C to 60 °C	(-40 °F to 140 °F)	
Humidity		0 % to 95 %		
Weight		0.75 kg	(1.65 lb)	
Dimensions				
	Height	12.5 cm	(4 <sup>15</sup> / <sub>16</sub> in)	
	Width	3.6 cm	(1 <sup>7</sup> / <sub>16</sub> in)	
	Depth	28.2 cm	(11 ¹/₀ in)	

#### **REMOTE CONTROL**

With IQS-500: GPIB (IEEE-488.1, IEEE-488.2) Ethernet and RS-232.

#### **INSTRUMENT DRIVERS**

LabVIEW™, SCPI commands and COM/DCOM librairies drivers

#### STANDARD ACCESSORIES


User guide; Certificate of Compliance; Test Report

#### LASER SAFETY



21 CFR 1040.10 and 1040.11 IEC 60825-1:1993+A1:1997+A2:2001: CLASS 1M LASER PRODUCT

#### **ORDERING INFORMATION**



Corporate Headquarters > 400 Godin Avenue, Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 | Fax: 1 418 683-2170 | info@exfo.com

		Toll-free: 1 800 663-3936 (USA and Canada)   www.exto.com			
EXFO America	4275 Kellway Circle, Suite 122	Addison, TX 75001 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164	
EXFO Europe	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85	Fax: +33.1.40.83.04.42	
EXFO Asia-Pacific	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242	
EXFO China	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662	
	No. 6 Southern Capital Gym Road				

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at http://www.exfo.com/specs

For the most recent version of this spec sheet, please go to the EXFO website at http://
In case of discrepancy, the Web version takes precedence over any printed literature.





